


Fine filter
LFMB-3/8-D-MINI-A-NPT
 Part number: 173713

FESTO



Data sheet

Feature	Value
Series	D
Size	Mini
Type code	LFMB
Grade of filtration	1 µm
Condensate drain	Fully automatic
Symbol	00991520
Operating pressure	2 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:7:3] Inert gas
Max. standard flow rate for air quality class	675 l/min
Min. standard flow rate for air quality class	125 l/min
Filter efficiency	99.99 %
Bowl guard	Metal bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Residual oil content	0.5 mg/m ³
Type of mounting	Optionally: Line installation With mounting bracket
Mounting position	Vertical
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Housing material	Die-cast zinc
Compressed air filter material	Borosilicate fiber
Material of bowl	PC
Note on materials	Free of copper and PTFE RoHS-compliant