


Air preparation unit FRC-3/4-D-5M-MIDI-NPT

FESTO

Part number: 173872



Data sheet

| Feature | Value |
|--|--|
| Size | Midi |
| Type code | FRC |
| Mounting position | Vertical |
| Condensate drain | Manual, non-detenting |
| Grade of filtration | 5 µm |
| Symbol | 00991549 |
| Operating pressure | 1 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Standard nominal flow rate | 2100 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [-:9:-] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:-] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1440 g |
| Type of mounting | Optionally: Line installation With mounting bracket |
| Pneumatic connection 1 | 3/4 NPT |
| Pneumatic connection 2 | 3/4 NPT |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |