

# Quick coupling EAMC-40-66-20-24

Part number: 176034

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	20 mm
Diameter of holder 2	24 mm
Size	40
Nominal length	66 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	6500 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	42.3 kgmm <sup>2</sup>
Transferable torque	21 Nm
Product weight	139 g
Note on materials	RoHS-compliant