

Quick coupling EAMC-40-66-XX-15

Part number: 176036

FESTO



Data sheet

Feature	Value
Diameter of holder 2	15 mm
Size	40
Nominal length	66 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	6500 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	42.3 kgmm ²
Product weight	139 g
Note on materials	RoHS-compliant