

Valve kit CPV10-BS-5/3G-M7

Part number: 176055

FESTO



Data sheet

Feature	Value
Valve function	5/3, closed
Pneumatic working port	M7
Operating pressure	2.5 bar ... 10 bar
Type code	CPV10
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	23 g
Type of mounting	With through-hole
Pneumatic connection 2	M7
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Die-cast zinc