

# Clevis flange SUA-50-R3

Part number: 176888

FESTO



## Data sheet

| Feature                          | Value                                             |
|----------------------------------|---------------------------------------------------|
| Size                             | 50                                                |
| Type code                        | SUA                                               |
| Mounting position                | Any                                               |
| Variants                         | High corrosion protection                         |
| Corrosion resistance class (CRC) | 3 - High corrosion stress                         |
| Product weight                   | 283 g                                             |
| Note on materials                | Free of copper and PTFE<br>RoHS-compliant         |
| Mounting material                | Wrought aluminum alloy<br>With protective coating |
| Bolt material                    | High-alloy stainless steel                        |
| Sleeve material                  | Spring steel                                      |
| Material of bearing              | Polymer                                           |
| Material of screws               | High-alloy stainless steel                        |
| Fuse material                    | High-alloy stainless steel                        |
| Shaft material                   | High-alloy stainless steel                        |