

# Plug socket with cable KMPV-SUB-D-15-10

Part number: 177674

FESTO



## Data sheet

Feature	Value
Type code	KMPV
Type of mounting	With through-hole
Mounting position	Any
Product weight	400 g
Electrical connection	15-pin Socket Sub-D
DC operating voltage range	≤30 V
Current rating	2.8 A
Cable length	10 m
Cable diameter	8.2 mm
Cable design	15 x 0.25 mm <sup>2</sup>
Degree of protection	IP65
Ambient temperature	-20 °C ... 80 °C
Material of cable sheath	PUR
Housing material	PBT-reinforced
Material of pin contacts	Copper alloy Gold-plated