


Rotary actuator DRVS-32-180-P

Part number: 1845720

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 32 |
| Cushioning angle | 0.5 deg |
| Swivel angle | 0 deg ... 180 deg |
| Type code | DRVS |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Structural design | Rotary vane |
| Position sensing | For proximity sensor |
| Symbol | 00991265 |
| Variants | Spigot shaft |
| Operating pressure | 0.2 MPa ... 0.8 MPa |
| Operating pressure | 2 bar ... 8 bar |
| Max. swivel frequency at 6 bar | 3 Hz |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | 0 °C ... 60 °C |
| Max. axial force | 75 N |
| Max. radial force | 200 N |
| Theoretical torque at 6 bar | 10 Nm |
| Permissible mass moment of inertia | 0.02 kgm ² |
| Product weight | 912 g |
| Type of mounting | With internal thread |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Drive shaft material | Steel, nickel-plated |
| Seals material | TPE-U(PU) |
| Housing material | Die-cast aluminum Painted |