

# Plug socket NTSD-WD-9

Part number: 18527

FESTO



## Data sheet

Feature	Value
Type code	NTSD
Type of mounting	With union nut
Mounting position	Any
Product weight	30 g
Electrical connection	4-pin Socket, angled Screw terminal
Operating voltage range AC	≤250 V
Current rating	16 A
Cable fitting	Pg9
Approved cable diameter	6 mm ... 8 mm
Connection cross section	1.5 mm <sup>2</sup>
Degree of protection	IP67
Ambient temperature	-5 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Housing material	PBT
Material of pin contacts	Copper alloy Brass