

Connection block VIGI-04-D-3

Part number: 18841

FESTO



Data sheet

| Feature | Value |
|-----------------------------|---|
| Type code | VIGI |
| Based on norm | ISO 5599-2 |
| Max. no. of valve positions | 1 |
| Operating pressure | -0.9 bar ... 16 bar |
| Certification | UL - Recognized (OL) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Temperature of medium | -10 °C ... 60 °C |
| Degree of protection | IP65 |
| Ambient temperature | -10 °C ... 60 °C |
| Sub-base mounting type | With through-hole |
| Pneumatic connection 1 | G1 |
| Pneumatic connection 2 | G1/2 |
| Pneumatic connection 3 | G1 |
| Pneumatic connection 4 | G1/2 |
| Pneumatic connection 5 | G1 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast aluminum |