

Vacuum suction cup holder ESH-HA-2-QS

Part number: 189195

FESTO



Data sheet

Feature	Value
Volume	0.501 cm ³
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at top
Classification of suction cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	12 g
Type of mounting	With lock nut
Suction cup mounting	Diameter 4 mm
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Seals material	NBR
Retaining bracket material	Aluminum Brass, nickel-plated POM High-alloy steel Tempered steel