

Vacuum suction cup holder ESH-HCL-1-PK

Part number: 189224

FESTO



Data sheet

Feature	Value
Suction cup holder height compensator	10 mm
Volume	0.36 cm ³
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	19 g
Type of mounting	With lock nut
Suction cup mounting	Diameter 3 mm
Vacuum connection	PK-3
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retaining bracket material	Aluminum Tempered steel High-alloy steel Brass, nickel-plated POM