

# Vacuum suction cup holder ESH-HD-4-PK

Part number: 189240

FESTO



## Data sheet

| Feature                               | Value   |
|---------------------------------------|---|
| Suction cup holder height compensator | 6 mm  |
| Volume                                | 0.449 cm <sup>3</sup>   |
| Type code                             | ESH   |
| Mounting position                     | Vertical  |
| Structural design                     | Vacuum connection at side<br>with height compensation                         |
| Classification of suction cup holder  | Size 4  |
| Operating medium                      | Atmospheric air based on ISO 8573-1:2010 [7::-]                               |
| Corrosion resistance class (CRC)      | 1 - Low corrosion stress  |
| Ambient temperature                   | -10 °C ... 60 °C  |
| Product weight                        | 43 g  |
| Type of mounting                      | With lock nut   |
| Suction cup mounting                  | M6  |
| Vacuum connection                     | PK-4  |
| Note on materials                     | RoHS-compliant  |
| Seals material                        | NBR<br>Steel  |
| Retaining bracket material            | Aluminum<br>High-alloy steel<br>Tempered steel<br>Brass, nickel-plated<br>POM |