

# Vacuum suction cup holder ESH-HD-5-G

FESTO

Part number: 189241



## Data sheet

Feature	Value
Suction cup holder height compensator	10 mm
Volume	2.072 cm <sup>3</sup>
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at side with height compensation
Classification of suction cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	195 g
Type of mounting	With lock nut
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Retaining bracket material	Aluminum Brass, nickel-plated Tempered steel High-alloy steel POM