

Vacuum suction cup holder ESH-HDL-6-G

Part number: 189252

FESTO



Data sheet

Feature	Value
Suction cup holder height compensator	40 mm
Volume	16.968 cm ³
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at side with height compensation
Classification of suction cup holder	Size 6
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	560 g
Type of mounting	With lock nut
Suction cup mounting	M20x2
Vacuum connection	G1/4
Note on materials	RoHS-compliant
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel