

# Vacuum suction cup holder ESH-HF-1-M10X1

Part number: 189260

FESTO



## Data sheet

Feature	Value
Suction cup holder height compensator	2.6 mm
Nominal width	2 mm
Volume	0.108 cm <sup>3</sup>
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	14 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	Diameter 3 mm
Vacuum connection	M10x1
Note on materials	RoHS-compliant
Seals material	NBR POM
Retaining bracket material	Tempered steel