

Flat cable KASI-1,5-Y-100

Part number: 18940

FESTO



Data sheet

Feature	Value
Type code	KASI
Product weight	71 g
DC operating voltage range	≤75 V
Operating voltage range AC	≤60 V
Current rating	3 A
Cable length	100 m
Degree of protection	IP65 With sealed wire ends
Ambient temperature	-40 °C ... 85 °C
Ambient temperature with flexible cable installation	-25 °C ... 85 °C
Material of cable sheath	Rubber compound
Color cable sheath	Yellow