


Vacuum cup without connector ESV-50-SNA

Part number: 190998

FESTO



Data sheet

Feature	Value
Min. workpiece radius	330 mm
Suction cup diameter	50 mm
Suction cup volume	2.387 cm ³
Type code	ESV
Connection position	Top
Mounting position	Any
Special features	Anti-static
Symbol	00991485
Suction cup shape	Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	105 N
Product weight	11.2 g
Color	Black/white dot
Shore hardness	50 +/- 5
Note on materials	Free of copper and PTFE RoHS-compliant
Suction cup material	BR