

Vacuum cup without connector ESV-60-SU

Part number: 191000

FESTO



Data sheet

Feature	Value
Min. workpiece radius	350 mm
Suction cup diameter	60 mm
Suction cup volume	3.953 cm ³
Type code	ESV
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 60 °C
Holding force at nominal operating pressure	166.1 N
Product weight	22 g
Color	Blue
Shore hardness	60 +/- 5
Note on materials	Free of copper and PTFE Contains paint-wetting impairment substances RoHS-compliant
Suction cup material	PUR