

# Vacuum cup without connector ESV-30-EN

Part number: 191027

FESTO



## Data sheet

Feature	Value
Min. workpiece radius	50 mm
Suction cup diameter	30 mm
Suction cup volume	1.952 cm <sup>3</sup>
Type code	ESV
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, extra-deep
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	37.2 N
Product weight	2.9 g
Color	Black
Shore hardness	60 +/- 5
Note on materials	Free of copper and PTFE RoHS-compliant
Suction cup material	NBR