


Vacuum cup without connector ESV-80-EF

Part number: 191046

FESTO



Data sheet

Feature	Value
Min. workpiece radius	160 mm
Suction cup diameter	80 mm
Suction cup volume	44.18 cm ³
Type code	ESV
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, extra-deep
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C ... 200 °C
Holding force at nominal operating pressure	275 N
Product weight	41 g
Color	Gray
Shore hardness	60 +/- 5
Note on materials	Free of copper and PTFE RoHS-compliant
Suction cup material	FPM