

Vacuum cup without connector ESV-20-BS

Part number: 191056

FESTO



Data sheet

| Feature | Value |
|---|---|
| Suction cup height compensation | 6 mm |
| Min. workpiece radius | 40 mm |
| Suction cup diameter | 20 mm |
| Suction cup volume | 1.6 cm ³ |
| Type code | ESV |
| Connection position | Top |
| Mounting position | Any |
| Symbol | 00991485 |
| Suction cup shape | Round bellows, 1.5 convolutions |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -30 °C ... 180 °C |
| Holding force at nominal operating pressure | 12.9 N |
| Product weight | 1.9 g |
| Color | Transparent |
| Shore hardness | 50 +/- 5 |
| Note on materials | Free of copper and PTFE Contains paint-wetting impairment substances RoHS-compliant |
| Suction cup material | VMQ (silicone) |