

Angle compensator ESWA-4

FESTO

Part number: 191206



Data sheet

Feature	Value
Angle compensator +/-	15 deg
Type code	ESWA
Mounting position	Any
Structural design	Ball joint
Classification of suction cup holder	Size 4
Operating pressure	-0.95 bar ... 4 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	19 g
Type of mounting	With external thread
Suction cup mounting	M6
Pneumatic connection	M6
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum Brass, nickel-plated