

# Illuminating seal ME-LD-12-24DC

Part number: 19141

FESTO



## Data sheet

Feature	Value
Type code	ME-LD
Switching position indication	LED
Type of mounting	On air solenoid valve with M3 central screw
Product weight	0.6 g
Electrical connection	Rectangular design, MSE
DC operating voltage range	12 V ... 24 V
Protective earth connection	Available
Nominal power luminous seal	0.05 W
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
Housing material	TPE-U(PU)