


Pressure switch PEV-1/4-B-M12

Part number: 192488

FESTO



Data sheet

Feature	Value
Type code	PEV
Conforms to standard	EN 60947-5-1
Symbol	00991472
Certification	CCC c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU low voltage directive
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Note on materials	RoHS-compliant
Measured variable	Relative pressure
Method of measurement	Pneumatic/electric pressure transducer
Operating pressure	0.1 MPa ... 1.2 MPa
Operating pressure	1 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-20 °C ... 80 °C
Ambient temperature	-20 °C ... 80 °C
Switching element function	Changeover switch
Max. switching frequency	3 Hz
Max. switching output voltage AC	48 V
Max. switching output voltage DC	48 V
Max. output current	4000 mA
Minimum load current	1 mA at 24 V 10 mA at 10 V 100 mA at 5V
Utilization category for inductive load	AC-14 DC-13
Utilization category for ohmic load	AC-12 DC-12
Electrical connection	4-pin M12x1 Plug as per EN 60947-5-2 Round design
Type of mounting	With through-hole
Mounting position	Any

Feature	Value
Pneumatic connection	G1/4
Product weight	194 g
Housing material	Die-cast aluminum
Switching contact material	Silver
Setting range threshold value	1 bar ... 12 bar
Degree of protection	IP65
Corrosion resistance class (CRC)	2 - Moderate corrosion stress