


Bellow cylinder EB-325-215

Part number: 193790

FESTO



Data sheet

Feature	Value
Size	325
Required installation Ø	340 mm
Stroke	215 mm
Max. height, advanced	305 mm
Max. angle of inclination	20 deg
Max. offset	20 mm
Min. installation height	75 mm
Type code	EB
Mode of operation	Single-acting
Symbol	00991205
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 70 °C
Resetting force	300 N
Product weight	4800 g
Type of mounting	With internal thread
Pneumatic connection	G1/4
Note on materials	Free of copper and PTFE RoHS-compliant
Bellows material	NR/BR
Housing material	Steel Galvanized