

Flat cylinder DZF-1"-1/2"-P-A

Part number: 194168

FESTO



Data sheet

Feature	Value
Stroke	12.7 mm
Piston diameter	1"
Max. angle of rotation of the piston rod +/-	1 deg
Type code	DZF
Cushioning	Elastic cushioning rings/pads at both ends
Mode of operation	Double-acting
Symbol	00991217
Protection against torsion/guide	Oval piston
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 6 bar, retracting	247 N
Theoretical force at 6 bar, advancing	295 N
Moving mass at 0 mm stroke	40 g
Additional weight per 10 mm stroke	6 g
Basic weight with 0 mm stroke	168 g
Additional moving mass per 10 mm stroke	13 g
Pneumatic connection	10-32 UNF-2B
Cover material	Aluminum
Seals material	FPM TPE-U(PU)
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel