

Flat cylinder DZF-2"-2"-A-P-A

Part number: 194239

FESTO



Data sheet

Feature	Value
Stroke	50.8 mm
Piston diameter	2"
Max. angle of rotation of the piston rod +/-	0.5 deg
Type code	DZF
Cushioning	Elastic cushioning rings/pads at both ends
Mode of operation	Double-acting
Symbol	00991217
Protection against torsion/guide	Oval piston
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 6 bar, retracting	990 N
Theoretical force at 6 bar, advancing	1178 N
Moving mass at 0 mm stroke	219 g
Additional weight per 10 mm stroke	25 g
Basic weight with 0 mm stroke	854 g
Additional moving mass per 10 mm stroke	9 g
Pneumatic connection	1/4 NPT
Cover material	Aluminum
Seals material	FPM TPE-U(PU)
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy steel