

Push-in L-connector CQL-28

Part number: 194587

FESTO



Data sheet

Feature	Value
Nominal width	24.9 mm
Type code	CQL
Mounting position	Any
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-25 °C ... 70 °C
Product weight	106 g
Pneumatic connection 1	For piping system/pneumatic tubing outside diameter of 28 mm
Pneumatic connection 2	for piping system/pneumatic tubing outside diameter of 28 mm
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	POM
Releasing ring material	POM
Material of tube retaining claw	High-alloy stainless steel