


Pressure regulator LRS-3/4-D-7-O-MIDI

Part number: 194654

FESTO



Data sheet

| Feature | Value |
|--|---|
| Size | Midi |
| Type code | LRS |
| Series | D |
| Actuator lock | Rotary knob with integrated lock |
| Mounting position | Any |
| Structural design | Directly controlled diaphragm regulator |
| Controller function | Outlet pressure constant With primary pressure compensation With secondary exhausting |
| Symbol | 00991540 |
| Pressure gauge | G1/4 prepared |
| Operating pressure | 0 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 7 bar |
| Max. pressure hysteresis | 0.2 bar |
| Standard nominal flow rate | 4500 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1180 g |
| Type of mounting | Front panel mounting Line installation With accessories |
| Pneumatic connection 1 | G3/4 |
| Pneumatic connection 2 | G3/4 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast zinc |
| Seals material | NBR |
| Housing material | Die-cast zinc |