

Mounting plate VN-T6-BP-NRH

Part number: 196956

FESTO



Data sheet

Feature	Value
Type code	VN
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	0.8 Nm
Product weight	12.4 g
Type of mounting	With through-hole With H-rail
Note on materials	Free of copper and PTFE RoHS-compliant
Plate material	PA-reinforced
Gate valve material	POM