

# Fluid separator CQA-28

Part number: 196984

FESTO



## Data sheet

Feature	Value
Nominal width	20 mm
Type code	CQA
Mounting position	Vertical
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-25 °C ... 75 °C
Ambient temperature	-25 °C ... 70 °C
Product weight	18 g
Pneumatic connection 1	Push-in sleeve CQ-28
Pneumatic connection 2	Push-in sleeve CQ-28
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	Brass