

Manifold

MHA2-PR6-3-M5

Part number: 197449

FESTO



Data sheet

Feature	Value
Type code	MH2
Max. no. of valve positions	6
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Sub-base mounting type	With through-hole With H-rail
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1/32	M7
Pneumatic connection 2	M5
Pneumatic connection 3/11	M7
Note on materials	Free of copper and PTFE
Material of sub-base	Wrought aluminum alloy