

Spiral plastic tubing PUN-12X2-S-2-BL

Part number: 197600

FESTO



Data sheet

| Feature | Value |
|--|---|
| Working length | 2 m |
| Outside diameter | 12 mm |
| Block length | 0.452 m |
| Inside diameter | 8 mm |
| Winding diameter | 95 mm |
| Number of windings | 20 |
| Type code | PUN-S |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Certification | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0506 00 |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Ambient temperature | -35 °C ... 60 °C |
| Product weight | 420 g |
| Pneumatic connection | For plug connection outside diameter 12 mm |
| Color | Blue |
| Shore hardness | D 52 +/-3 |
| Note on materials | Free of copper and PTFE |
| Material of pneumatic tubing | TPE-U(PU) |