

# Quick coupling EAMC-30-32-10-10

Part number: 2310372

FESTO



## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Diameter of holder 1   | 10 mm                  |
| Diameter of holder 2   | 10 mm                  |
| Size                   | 30                     |
| Nominal length         | 32 mm                  |
| Type code              | EAMC                   |
| Mounting position      | Any                    |
| Max. rotational speed  | 8000 1/min             |
| Storage temperature    | -25 °C ... 60 °C       |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -25 °C ... 60 °C       |
| Mass moment of inertia | 5.87 kgmm <sup>2</sup> |
| Transferable torque    | 12.5 Nm                |
| Product weight         | 48 g                   |
| Note on materials      | RoHS-compliant         |