

Pneumatic muffler U-3/4

Part number: 2311

FESTO



Data sheet

Feature	Value
Type code	U
Mounting position	Any
Symbol	00991473
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	17600 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Noise level	85 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	83 g
Pneumatic connection	G3/4
Cushioning insert material	PE
Note on materials	Free of copper and PTFE RoHS-compliant