


# Precision pressure regulator

## LRP-7.0-6

Part number: 2418761

FESTO



## Data sheet

Feature	Value
Size	40
Type code	LRP
Series	LR
Actuator lock	Rotary knob with detent
Mounting position	Any
Structural design	Pilot-controlled precision diaphragm regulator
Controller function	Outlet pressure constant With secondary exhausting
Symbol	00991540
Pressure gauge	G1/8 prepared
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Pressure regulation range	0.1 bar ... 6 bar
Max. pressure hysteresis	0.02 bar
Standard nominal flow rate	240 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-10 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	200 g
Type of mounting	Front panel mounting Line installation With accessories
Pressure gauge connection	G1/8
Pneumatic connection 1	For sub-base Ø 7 mm
Pneumatic connection 2	for sub-base Ø 7 mm
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum
Diaphragm material	NBR