

Clamping sleeve EAMH-60-9-C18.1

Part number: 2428518

FESTO



Data sheet

Feature	Value
Size	60
Type code	EAMH
Mounting position	Any
Max. rotational speed	6000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	1.42 kgmm ²
Product weight	32 g
Note on materials	RoHS-compliant