

Axial kit EAMM-A-D50-80G-S1

Part number: 2734291



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C ... 60 °C
Transferable torque	17 Nm
Product weight	1190 g
Interface code, actuator	D50B
Interface code, motor in	80G
Note on materials	Contains paint-wetting impairment substances RoHS-compliant