

Parallel kit EAMM-U-70-D32-60G-96

Part number: 2748181

FESTO



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Size | 70 |
| Type code | EAMM-U |
| Mounting position | Any |
| Gear ratio | 1:1 |
| Max. rotational speed | 5000 1/min |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 118 kgmm ² |
| No-load driving torque | 0.18 Nm |
| Transferable torque | 7 Nm |
| Product weight | 1760 g |
| Note on materials | RoHS-compliant |