

# Clamping sleeve EAMH-86-10-C27.3-P

Part number: 2789365

FESTO



## Data sheet

| Feature                | Value               |
|------------------------|---------------------|
| Size                   | 86                  |
| Type code              | EAMH                |
| Mounting position      | Any                 |
| Max. rotational speed  | 5000 1/min          |
| Storage temperature    | -25 °C ... 60 °C    |
| Relative air humidity  | 0 - 95 %            |
| Ambient temperature    | -10 °C ... 60 °C    |
| Mass moment of inertia | 9 kgmm <sup>2</sup> |
| Product weight         | 115 g               |
| Note on materials      | RoHS-compliant      |