


Parallel kit EAMM-U-110-D50-60H-120

Part number: 2798760

FESTO



Data sheet

Feature	Value
Size	110
Type code	EAMM-U
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	799 kgmm ²
No-load driving torque	0.3 Nm
Transferable torque	25 Nm
Product weight	5280 g
Note on materials	RoHS-compliant