

Bellows kit EADB-V2-32-S301-400

Part number: 2828832

FESTO



Data sheet

Feature	Value
Outside diameter	57 mm
Size	32
Stroke range	301 mm ... 400 mm
Piston rod extension	121 mm
Type code	EADB
Design	Round
Mounting position	Any
Structural design	Bellows kit with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-10 °C ... 80 °C
Moving mass	143 g
Product weight	212 g
Type of mounting	Push-on With threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Adaption parts material	Wrought aluminum alloy Anodized
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel