

Connection block MRS-2

Part number: 2844247

FESTO



Data sheet

Feature	Value
Size	2
Type code	MRS
Max. no. of valve positions	2
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Max. tightening torque for valve mounting	2.5 Nm
Max. tightening torque for wall mounting	4 Nm
Product weight	365 g
Pneumatic connection 1	G3/8
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy