

Clevis flange CRSNCS-80

Part number: 2895924

FESTO



Data sheet

Feature	Value
Size	80
Type code	CRSNCS
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Variants	High corrosion protection
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	1173 g
Note on materials	RoHS-compliant
Mounting material	High-alloy stainless steel
Rod end bearing material	PTFE Stainless steel
Material of screws	High-alloy stainless steel