

Front unit ERMH-11-E17-30

Part number: 3385153

FESTO



Data sheet

Feature	Value
Size	11
Type code	ERMH
Structural design	Electromechanical rotary module
Mounting position	Any
Rotation angle	Infinite
Gear ratio	30:1
Nominal torque	1.8 Nm
Repetition accuracy	±0.01 °
Max. axial force	300 N
Product weight	1298 g
Duty cycle	100%
Motor nominal current	0.74 A
Motor type	Servo motor
Max. output speed	200 1/min
Nominal operating voltage AC	230 V
Motor nominal power	22.1 W
Peak current	1.5 A
Max. pull-out torque static	40 Nm
Peak torque	4.5 Nm
Permissible mass moment of inertia of load	0.006 kgm ²
Degree of protection	IP40
Ambient temperature	0 °C ... 40 °C
Note on materials	RoHS-compliant