

Plug socket MSSD-F

Part number: 34431

FESTO



Data sheet

Feature	Value
Type code	MSSD
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	17 g
Electrical connection	3-pin Socket, angled Rectangular design MSF
Cable fitting	Pg9
Cable diameter	6 mm ... 8 mm
Nominal conductor cross section	≤1.5 mm ²
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
Housing material	Polymer
Housing colour	Black