

Quick connector CK-M5-PK-4

Part number: 3562

FESTO



Data sheet

Feature	Value
Nominal width	2.9 mm
Type code	CK
Type of seal on screwed trunnion	Sealing ring
Mounting position	Any
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	External thread M5
Pneumatic connection 2	for pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant
Housing material	Aluminum