

Barb tubing fitting N-1/8-P-6

Part number: 3605

FESTO



Data sheet

Feature	Value
Nominal width	4.5 mm
Type code	N
Type of seal on screwed trunnion	Sealing ring
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Pneumatic connection 1	External thread G1/8
Pneumatic connection 2	For tubing I.D. 6 mm
Note on materials	RoHS-compliant