

Axial kit EAMM-A-S38-40A-G2

Part number: 3637971

FESTO



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	6.5 Nm
Product weight	270 g
Interface code, actuator	S38
Interface code, motor in	40A
Note on materials	RoHS-compliant